

D4" Spiral Wound Nanofiltration Elements

Description: High Rejection, High Productivity:
High pressure application for nanofiltration


Specifications:

Model	Permeate Flow GPD(m³/day)	Active Membrane Area ft²(m²)	Stabilized Salt Rejection	Minimum Salt Rejection	Feed spacer mil(mm)	Test Conditions
NF-4040-HP	2100 (8)	90 (8. 4)	99%	98%	28 (0. 7)	100psi /2000ppm MgSO₄
	2000 (8)		40~60%			70psi /500ppm NaCl

1. All performance data are collected at 25°C (77°F), pH7.5 and 15% recovery rate.
2. Permeate flows for single element may vary ±15%.

Element Dimension:

* Unit: Inch (mm)
1 inch= 25.4 mm



Operating Limits for Design:

Maximum Operating Temperature.....	45°C(113°F)
Maximum Operating Pressure.....	1200psi(83bar)
Maximum Pressure Drop (single element).....	15psi(1.0bar)
pH Range for Continuous Operation.....	3-10
pH Range for Cleaning.....	2-11
Chlorine tolerance.....	<0.1ppm
Maximum Feed SDI.....	5

