

8" Spiral Wound Nanofiltration Elements

Description:


Low Pressure, High Productivity:
Low pressure application for nanofiltration

Specifications:

Model	Permeate Flow GPD(m ³ /day)	Active Membrane Area ft ² (m ²)	Stabilized Salt Rejection	Minimum Salt Rejection	Feed spacer mil(mm)	Test Conditions
NF-8040-400-HF	7900 (30)	400 (37)	95%	93%	28 (0.7)	30psi/2000ppm MgSO ₄
	9500 (36)		15~20%	15~20%		30psi/500ppm NaCl

1. All performance data are collected at 25°C (77°F), pH7.5 and 15% recovery rate.
2. Permeate flows for single element may vary ±15%.

Element Dimension:



Product	Dimensions – Inches (mm)		
	A	B	C
NF-8040-400-HF	40.0 (1016)	1.125 (29)	7.9 (201)

* 1 inch= 25.4 mm

Operating Limits for Design:

Maximum Operating Temperature	45°C(113°F)
Maximum Operating Pressure	600psi(41bar)
Maximum Pressure Drop (single element)	15psi(1.0bar)
pH Range for Continuous Operation	3-10
pH Range for Cleaning	2-11
Chlorine tolerance	<0.1ppm
Maximum Feed SDI	5

