

8" Spiral Wound Nanofiltration Elements

Description:


Low Pressure, High Productivity:
Low pressure application for nanofiltration

Specifications:

Model	Permeate Flow GPD(m ³ /day)	Active Membrane Area ft ² (m ²)	Stabilized Salt Rejection	Minimum Salt Rejection	Feed spacer mil(mm)	Test Conditions
NF-8040-400 (34)	11800 (45)	400 (37)	98%	97%	34 (0.85)	70psi/2000ppm MgSO ₄
	13800 (52)		40~60%	40~60%		70psi/500ppm NaCl

1. All performance data are collected at 25°C (77°F), pH7.5 and 15% recovery rate.
2. Permeate flows for single element may vary ±15%.

Element Dimension:



Product	Dimensions – Inches (mm)		
	A	B	C
NF-8040-400(34)	40.0 (1016)	1.125 (29)	7.9 (201)

* 1 inch= 25.4 mm

Operating Limits for Design:

Maximum Operating Temperature.....	45°C(113°F)
Maximum Operating Pressure.....	600psi(41bar)
Maximum Pressure Drop (single element).....	15psi(1.0bar)
pH Range for Continuous Operation.....	3-10
pH Range for Cleaning.....	2-11
Chlorine tolerance.....	<0.1ppm
Maximum Feed SDI.....	5

